



CB4E19D50G7TN Flexible Copper Covered Braid

By Burndy
Catalog # [CB4E19D50G7TN](#)

Flexible Copper Covered Braid.



General

Connector Type	Braid
Insulation	Y
Material	Copper
Material - Ferrules	Y
Physical Attribute - Number of Braids	4
Plated	Y
UPC	781810353578
UPC 12 Digit	7818103535788

Dimensions

Dimension - L Length Overall mm	495 mm
Dimension - Length Overall inch	19.50 in
Length	19.5 in

Electrical Ratings

Rating - Outdoor Amperage	800
---------------------------	-----

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	EX
UL Listed	No

Logistics

Minimum Pack Quantity	1
-----------------------	---

Product Assets

[Catalogs - Full Line BURNDY Catalog](#)
[Sales Drawings - 10034686](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
BRDY-CB4E19D50G7TN-SPEC-EN | REV 1/2024