



## CB4G18N Flexible Copper Covered Braid

By Burndy  
Catalog # [CB4G18N](#)

Flexible Copper Covered Braid.



### Features

- Most Burndy braid are UL Listed and CSA Certified
- Pressed seamless copper ferrules provide added durability and prevent fraying, providing extra strength for a robust bonding connection
- Braid is especially suited for applications that require flexibility or resistance to vibration
- Extra fine stranding gives enhanced flexibility
- Ferrules clearly marked with Burndy braid type and UL markings (where appropriate)
- Available in custom lengths and hole sizes to suit your needs (contact your local sales representative for non-standard configurations)
- For assistance in finding the perfect braid for your needs click [here](#) for our Braid Configurator Tool:  
[www.hubbell.com/config/BRAID](http://www.hubbell.com/config/BRAID)

### General

Catalog Number	CB4G18N
Connector Type	Braid
Material	Copper
UPC	781810207116
UPC 12 Digit	7818102071166

### Dimensions

Length	18 in
--------	-------

### Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	EX
UL Listed	No

### Logistics

Carton Quantity	3
Minimum Pack Quantity	1
Pallet Quantity	270

### Product Assets

- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Specifications - CB4G18N](#)