



## CBD108G19 Flexible Copper Covered Braid

By Burndy  
Catalog # [CBD108G19](#)

Flexible Copper Covered Braid.



### General

Connector Type	Braid
Insulation	Y
Material	Copper
Material - Ferrules	Y
Physical Attribute - Number of Braids	1
Plated	Y
UPC	781810207062
UPC 12 Digit	7818102070622

### Dimensions

Dimension - L Length Overall mm	2743 mm
Dimension - Length Overall inch	108.00 in
Length	108 in

### Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	EX
UL Listed	No

### Logistics

Minimum Pack Quantity	1
-----------------------	---

### Product Assets

[Catalogs - Full Line BURNDY Catalog](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.  
BRDY-CBD108G19-SPEC-EN | REV 5/2024