



## CBD24N Insulated flexible tinned copper braid 24.00"x0.94"x0.13

By Burndy  
Catalog # [CBD24N](#)

Insulated flexible tinned copper braid 24.00"x0.94"x0.13.



### General

Catalog Number	CBD24N
Connector Type	Braid
Material	Copper
Material - Ferrules	Copper
Physical Attribute - Number of Braids	1
UPC	781810544815
UPC 12 Digit	7818105448155

### Dimensions

Dimension - L Length Overall mm	610
Dimension - Length Overall inch	24
Dimension - Width inch	0.94
Dimension - Width mm	24 mm
Length	24 in

### Electrical Ratings

Rating - Indoor Amperage	190 A
Rating - Outdoor Amperage	225 A

### Certifications And Compliance

Certification - CSA Approved	No
Standards - RoHS Compliance Status	CM

### Logistics

Carton Quantity	10
Minimum Pack Quantity	30
Pallet Quantity	900

### Product Assets

- [3D Models - CBD24N\\_MODEL-STEP](#)
- [3D Models - CBD24N\\_MODEL-PDF](#)
- [3D Models - CBD24N\\_MODEL-IGES](#)
- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Specifications - CBD24N](#)