



CBG13D50G5TN Flexible Copper Covered Braid

By Burndy
Catalog # [CBG13D50G5TN](#)

Tin Plated Ferrules.



General

| | |
|---------------------------------------|---------------|
| Connector Type | Braid |
| Insulation | Y |
| Material | Copper |
| Material - Ferrules | Y |
| Physical Attribute - Number of Braids | 1 |
| Plated | Y |
| UPC | 781810200025 |
| UPC 12 Digit | 7818102000255 |

Dimensions

| | |
|---------------------------------|----------|
| Dimension - L Length Overall mm | 343 mm |
| Dimension - Length Overall inch | 13.50 in |
| Length | 13.5 in |

Certifications And Compliance

| | |
|------------------------------------|----|
| Certification - CSA Approved | No |
| Certification - ETL | No |
| Certification - UL Recognized | No |
| Certification - cULus | No |
| Standards - RoHS Compliance Status | EX |
| UL Listed | No |

Logistics

| | |
|-----------------------|---|
| Minimum Pack Quantity | 1 |
|-----------------------|---|

Product Assets

[Catalogs - Full Line BURNDY Catalog](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
BRDY-CBG13D50G5TN-SPEC-EN | REV 5/2024