



CC3Y4/OL12G4 Flexible Rope Lay Copper Braid

By Burndy
Catalog # [CC3Y4/OL12G4](#)

Flexible Rope Lay Copper Braid.



Features

- Most Burndy braid are UL Listed and CSA Certified
- Pressed seamless copper ferrules provide added durability and prevent fraying, providing extra strength for a robust bonding connection
- Braid is especially suited for applications that require flexibility or resistance to vibration
- Extra fine stranding gives enhanced flexibility
- Ferrules clearly marked with Burndy braid type and UL markings (where appropriate)
- Available in custom lengths and hole sizes to suit your needs (contact your local sales representative for non-standard configurations)
- For assistance in finding the perfect braid for your needs click here for our Braid Configurator Tool: www.hubbell.com/config/BRAID

General

Catalog Number	CC3Y4/OL12G4
Connector Type	Rope lay
Material	Copper
Plating Type	Tin plated
UPC	621945468634

Dimensions

Dimension - Hole Size inch	0.69 in
----------------------------	---------

Dimension - L Length Overall mm	737 mm
Dimension - Length Overall inch	29 in
Length	12 in
Thickness	0.57 in
Weight	8.245 lb

Electrical Ratings

Amperage Rating	1000 A
-----------------	--------

Certifications And Compliance

Certification - CSA Approved	No
------------------------------	----

Logistics

Carton Quantity	10
Minimum Pack Quantity	5
Pallet Quantity	1680

Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
[Customer Notices - Prop 65 Notice](#)
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
[Specifications - BURNDY_CC3Y4OL12G4_Specsheet](#)
[Specifications - CC3Y4/OL12G4](#)