



CC3Y4/OL15D50G4 Flexible Rope Lay Copper Braid

By Burndy
Catalog # [CC3Y4/OL15D50G4](#)

Flexible Rope Lay Copper Braid.



Features

- Most Burndy braid are UL Listed and CSA Certified
- Pressed seamless copper ferrules provide added durability and prevent fraying, providing extra strength for a robust bonding connection
- Braid is especially suited for applications that require flexibility or resistance to vibration
- Extra fine stranding gives enhanced flexibility
- Ferrules clearly marked with Burndy braid type and UL markings (where appropriate)
- Available in custom lengths and hole sizes to suit your needs (contact your local sales representative for non-standard configurations)
- For assistance in finding the perfect braid for your needs click [here](#) for our Braid Configurator Tool:
www.hubbell.com/config/BRAID

General

Catalog Number	CC3Y4/OL15D50G4
Connector Type	Rope lay
Material	Copper
UPC	621945468641

Dimensions

Dimension - L Length Overall	394 mm
Dimension - Length Overall	15.50 in
Length	15.5 in

Certifications And Compliance

Certification - CSA Approved	No
------------------------------	----

Logistics

Carton Quantity	10
Minimum Pack Quantity	5
Pallet Quantity	960

Product Assets

- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Sales Drawings - 50072352](#)
- [Specifications - CC3Y4/OL15D50G4](#)
- [Specifications - BURNDY_CC3Y4OL15D50G4_Specsheet](#)