



CCFBGFR, Clear Cover, Flame retardant cover for YH8C8C or YH6C6C, #8-#6 AWG H-Tap

By Burndy
Catalog # [CCFBGFR](#)

Flame retardant H-retardant cover, #8-#6 AWG, Green.



Features

- Connector end stops
- Flexible fingers
- snap tight latches
- 2piece construction
- magnifying lens

Application

Cover

General

Catalog Number	CCFBGFR
Color	Clear
Color Code	Orange
Connector Type	H-TAP COVERS CLEAR
Material	POLYCARBONATE
Operating Temperature	90 °C
Plated	N
Plating Type	Unplated
Temperature Rating	194
UPC	781810438145
UPC 12 Digit	7818104381455

Dimensions

Dimension - Height inch	1.16 in
Dimension - L Length Overall mm	92 mm
Dimension - Length Overall inch	3.63 in
Dimension - Width inch	0.85 in

Electrical Ratings

Voltage - Maximum	35000
Voltage Rating	600 V

Conductor Related

Conductor - AL Str Size	8 AWG-6 AWG
Conductor - Copper Str	8 AWG-6 AWG
Compact Size	
Conductor - Copper Str Size	8 AWG-6 AWG
Conductor - Copper Str Size Range	#8 AWG-#6 AWG
Conductor - Material	COPPER
Conductor - Max Length	0.65 in
Conductor Type	CODE/FLEX
Wire Size	8 AWG-6 AWG

Certifications And Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance	CM
Status	
UL Listed	Yes

Logistics

Carton Quantity	100
Minimum Pack Quantity	1
Pallet Quantity	3300

Product Assets

[Catalogs - BURNDY Master Catalog - Section C - Compression Connections](#)
[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
[Customer Notices - Prop 65 Notice](#)
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
[Product Cross Section Image\(s\) - BUR_CCFOFR_LineArt](#)
[Sales Drawings - 10064550](#)
[Specifications - CCFBGFR](#)