



**CCFDXFR, Clear Cover, Flame
retardant cover for YH2929, 250
kcmil H-Tap**

By Burndy
Catalog # [CCFDXFR](#)

Flame retardant H-retardant cover, 250 kcmil, Purple.



Features

- Connector end stops
- Flexible fingers
- snap tight latches
- 2piece construction
- magnifying lens

Application

Cover

General

Catalog Number	CCFDXFR
Color	Clear
Color Code	Purple
Connector Type	H-TAP COVERS CLEAR
EU RoHS Indicator	Yes
Fire Resistance	Yes
Material	POLYCARBONATE
Operating Temperature	90 °C
Plated	N
Plating Type	Unplated
Sub Brand	FLAME RETARDENT COVER
Temperature Rating	194
Type	CCF-FR,Flame Retardant
UPC	781810452141
UPC 12 Digit	7818104521411

Dimensions

Dimension - Height inch	2.46 in
Dimension - L Length Overall mm	152 mm
Dimension - Length Overall inch	6 in
Dimension - Maximum Conductor Size Accommodated	250 kcmil
Dimension - Width inch	1.57 in

Electrical Ratings

Voltage - Maximum	35000
Voltage Rating	600 V

Conductor Related

Conductor - AL Str Size	250 KCMIL
Conductor - Copper Str	250 KCMIL
Compact Size	
Conductor - Copper Str Size	250 KCMIL
Conductor - Copper Str Size Range	250 kcmil
Conductor - Material	COPPER
Conductor - Max Length	0.95 in
Conductor Type	CODE/FLEX
Wire Size	250 KCMIL

Certifications And Compliance

Buy American Compliant	Yes
Certification - 94V0 Rated	Y
Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Carton Quantity	5
Minimum Pack Quantity	1
Pallet Quantity	450

Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
[Catalogs - BURNDY Master Catalog - Section C - Compression Connections](#)
[Customer Notices - Prop 65 Notice](#)
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
[Product Cross Section Image\(s\) - BUR_CCFOFR_LineArt](#)
[Sales Drawings - 10064550](#)
[Specifications - CCFDXFR](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
BRDY-CCFDXFR-SPEC-EN | REV 8/2024