



CCFNFR, Clear Cover, Flame retardant cover for YH3434, YH3429C, 500 kcmil H-Tap

By Burndy
Catalog # CCFNFR



Flame retardant H-retardant cover, 500 kcmil, Brown.

Features

- Connector end stops
- Flexible fingers
- snap tight latches
- 2piece construction
- magnifying lens

Application

Cover

General

Color	Clear
Color Code	Brown
Connector Type	H-TAP COVERS CLEAR
Fire Resistance	Yes
Material	POLYCARBONATE
Operating Temperature	90 °C
Plated	N
Plating Type	Unplated
Temperature Rating	194
UPC	781810438169
UPC 12 Digit	7818104381699

Dimensions

Dimension - Height inch	2.76 in
Dimension - L Length Overall mm	184 mm
Dimension - Length Overall inch	7.25 in
Dimension - Maximum Conductor Size Accommodated	500 kcmil
Dimension - Width inch	2.05 in

Electrical Ratings

Voltage - Maximum	35000
Voltage Rating	600 V

Conductor Related

Conductor - AL Str Size	500 KCMIL
Conductor - Copper Str Compact Size	500 KCMIL
Conductor - Copper Str Size	500 KCMIL
Conductor - Copper Str Size Range	500 kcmil
Conductor - Material	COPPER
Conductor - Max Length	1.10 in
Conductor Type	CODE/FLEX
Wire Size	500 KCMIL

Certifications And Compliance

Certification - 94V0 Rated	Y
Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Carton Quantity	10
Minimum Pack Quantity	1
Pallet Quantity	900

Product Assets

[Catalogs - Full Line BURNDY Catalog](#)
[Customer Notices - Prop 65 Notice](#)
[Product Cross Section Image\(s\) - BUR_CCFOFR_LineArt](#)
[Sales Drawings - 10064550](#)



A proud member of the Hubbell Family.

