



## **CCOFR, Clear Cover, Flame retardant cover for YH2C2C, #2 AWG H-Tap**

By Burndy  
Catalog # [CCOFR](#)

Clear Polycarbonate H-Tap-Flame Retardant Cover, #2AWG,  
600V.



## Features

- Connector end stops
- Flexible fingers
- snap tight latches
- 2piece construction
- magnifying lens

## Application

Cover

## General

Catalog Number	CCFOFR
Color	Clear
Color Code	Brown
Connector Type	H-TAP COVERS CLEAR
EU RoHS Indicator	Yes
Fire Resistance	Yes
Material	POLYCARBONATE
Operating Temperature	90 °C
Plated	N
Plating Type	Unplated
Sub Brand	CRIMPIT
Temperature Rating	194
Type	H-Tap Connector
UPC	781810438176
UPC 12 Digit	7818104381766

## Dimensions

Dimension - Height inch	1.44 in
Dimension - L Length Overall mm	112 mm
Dimension - Length Overall inch	4.42 in
Dimension - Maximum Conductor Size Accommodated	2 AWG
Dimension - Width inch	1.21 in

## Electrical Ratings

Voltage - Maximum	35000
Voltage Rating	600 V

## Conductor Related

Conductor - AL Str Size	2 AWG
Conductor - Copper Str	2 AWG
Compact Size	
Conductor - Copper Str Size	2 AWG
Conductor - Copper Str Size Range	#2 AWG
Conductor - Material	COPPER
Conductor - Max Length	0.80 in
Conductor Type	CODE/FLEX
Wire Size	2 AWG

## Certifications And Compliance

Buy American Compliant	Yes
Certification - 94V0 Rated	Y
Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	Yes

## Logistics

Carton Quantity	25
Minimum Pack Quantity	1
Pallet Quantity	2250

## Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)  
[Catalogs - BURNDY Master Catalog - Section C - Compression Connections](#)  
[Customer Notices - Prop 65 Notice](#)  
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)  
[Product Cross Section Image\(s\) - BUR\\_CCFOFR\\_LineArt](#)  
[Sales Drawings - 10064550](#)  
[Specifications - CCFOFR](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved  
BRDY-CCFOFR-SPEC-EN | REV 8/2024