



**CCFRFR, Clear Cover, Flame
retardant cover for YH83939,
YH3931, YH4429, YH4434,
YH4444, 750 kcmil and 1000 kcmil
H-Tap**

By Burndy
Catalog # [CCFRFR](#)

COPPER CRIMPIT™ C-Tap Connector; 750 - 1000 kcmil (Main
and Tap 1).



Features

- Connector end stops
- Flexible fingers
- snap tight latches
- 2piece contruction
- magnifying lens

Application

Cover

General

Color	Clear
Color Code	Yellow
Connector Type	H-TAP COVERS CLEAR
EU RoHS Indicator	Yes
Fire Resistance	Yes
Material	POLYCARBONATE
Operating Temperature	90 °C
Plated	N
Plating Type	Unplated
Sub Brand	CRIMPIT
Temperature Rating	194
Type	H-Tap Connector
UPC	781810438183
UPC 12 Digit	7818104381833

Dimensions

Dimension - Height inch	3.66 in
Dimension - L Length Overall mm	219 mm
Dimension - Length Overall inch	8.63 in
Dimension - Maximum Conductor Size Accommodated	1000 kcmil;750 kcmil
Dimension - Width inch	2.58 in

Electrical Ratings

Voltage - Maximum	35000
Voltage Rating	600 V

Conductor Related

Conductor - AL Str Size	1000 KCMIL-750 KCMIL
Conductor - Copper Str Compact Size	1000 KCMIL-750 KCMIL
Conductor - Copper Str Size	1000 KCMIL-750 KCMIL
Conductor - Copper Str Size Range	750 kcmil-1000 kcmil
Conductor - Material	COPPER
Conductor - Max Length	1.301.10 in
Conductor Type	CODE/FLEX
Wire Size	1000 KCMIL-750 KCMIL

Certifications And Compliance

Certification - 94V0 Rated	Y
Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Carton Quantity	5
Minimum Pack Quantity	1
Pallet Quantity	450

Product Assets

[Catalogs - Full Line BURNDY Catalog](#)
[Customer Notices - Prop 65 Notice](#)
[Product Cross Section Image\(s\) - BUR_CCFOFR_LineArt](#)
[Sales Drawings - 10064550](#)



A proud member of the Hubbell Family.

