



CCSC110600, Clear Cold Shrink, 6", .39"-.80" Jacket OD Range

By Burndy
Catalog # CCSC110600

Clear Cold Shrink.



Features

- Length of tube is consistent before and after application
- Easy, safe installation
- Suitable for wide range of cable sizes
- UV resistance, thermal stability
- No special tools or training required
- Forms a moisture resistant seal
- Indoor and outdoor applications
- Rip and Grip Installation does not require heat gun or any installation tools
- Passes TELCORDIA GR-347-CORE Abrasion and Cut Test up to 750 kcmil
- cUL insulating cover for wire connectors tested in accordance to UL 486A/B
- Passes UL 746C Glow Wire Test
- Ripcord is recyclable

Application

Cold Shrink, Rated to 2000 Volts, offer insulation and moisture resistant sealing for in-line cable connector systems

General

Catalog Number	CCSC110600
Color	<ul style="list-style-type: none">• Clear• Clear
Connector Type	CLEAR
Material	Silicone Rubber
UPC	621945524194

Dimensions

Diameter	0.28 in
Dimension - Diameter Max before Shrink inch	1.1
Length	5.91 in
Width	0.12 in

Electrical Ratings

Voltage Rating	2000 V
----------------	--------

Certifications And Compliance

Certification - CSA Approved	No
------------------------------	----

Logistics

Carton Quantity	500
Minimum Pack Quantity	1
Pallet Quantity	1500

Product Assets

[Catalog Page - BURNDY Page D2 & D3 - Cold Shrink](#)
[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
[Catalogs - Cable Accessories](#)
[Catalogs - BURNDY Master Catalog - Section D - Shrink Tubing](#)
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
[Sales Drawings - 50090656](#)
[Sell Sheets - Clear & Black Cold Shrink - Rated for 2000 Volts](#)
[Specifications - CCSC110600](#)
[Video - Grease Best Practices](#)