



## CCSC256900, Clear Cold Shrink, 9", 1.22"-2.01" Jacket OD Range

By Burndy  
Catalog # [CCSC256900](#)

Clear Cold Shrink, Specially formulated silicone rubber offering excellent insulation and moisture resistant sealing for in-line cable connector systems. The rubber sleeves are factory expanded over a removeable, plastic ripcord housing. Installs quickly and easily with no heat gun or other installation tools. Passes TELCORDIA GR-347-CORE Abrasion and Cut Test up to 750 kcmil. Operating temperature range: -40°C to +105°C.

### Features

- Length of tube is consistent before and after application
- Easy, safe installation
- Suitable for wide range of cable sizes
- UV resistance, thermal stability
- No special tools or training required
- Forms a moisture resistant seal
- Indoor and outdoor applications
- Rip and Grip Installation does not require heat gun or any installation tools
- Passes TELCORDIA GR-347-CORE Abrasion and Cut Test up to 750 kcmil
- cUL insulating cover for wire connectors tested in accordance to UL 486A/B
- Passes UL 746C Glow Wire Test
- Ripcord is recyclable

### Application

Cold Shrink, Rated to 2000 Volts, offer insulation and moisture resistant sealing for in-line cable connector systems

### General



Catalog Number	CCSC256900
Color	Clear
Material	Silicone Rubber
UPC	621945658356

### Dimensions

Length	9 in
--------	------

### Electrical Ratings

Voltage Rating	2000 V
----------------	--------

### Logistics

Carton Quantity	10
Pallet Quantity	720

### Product Assets

[Catalog Page - BURNDY Page D2 & D3 - Cold Shrink Catalogs - BURNDY Master Catalog - Section D - Shrink Tubing Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog Interactive Catalog - BURNDY Full-Line Digital Catalog Sell Sheets - Clear & Black Cold Shrink - Rated for 2000 Volts Specifications - CCSC256900](#)