



CCY10L12LT38G Covered Rope Lay Braid

By Burndy
Catalog # [CCY10L12LT38G](#)

Covered Rope Lay Braid.



Features

- Most Burndy braid are UL Listed and CSA Certified
- Pressed seamless copper ferrules provide added durability and prevent fraying, providing extra strength for a robust bonding connection
- Braid is especially suited for applications that require flexibility or resistance to vibration
- Extra fine stranding gives enhanced flexibility
- Ferrules clearly marked with Burndy braid type and UL markings (where appropriate)
- Available in custom lengths and hole sizes to suit your needs (contact your local sales representative for non-standard configurations)
- For assistance in finding the perfect braid for your needs click here for our Braid Configurator Tool: www.hubbell.com/config/BRAID

General

Catalog Number	CCY10L12LT38G
Connector Type	Rope lay
Material	Copper
UPC	781810674550
UPC 12 Digit	7818106745500

Dimensions

Dimension - L Length Overall	319.53 mm
mm	
Dimension - Length Overall	12.58 in
inch	
Length	12 in

Certifications And Compliance

Certification - CSA Approved	No
Standards - RoHS Compliance	CM
Status	

Logistics

Carton Quantity	50
Minimum Pack Quantity	1
Pallet Quantity	4500

Product Assets

- [Catalogs - BURNDY Master Catalog - Section E2 - Mechanical Grounding](#)
- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Sales Drawings - 50049701](#)
- [Specifications - CCY10L12LT38G](#)