



CCY10L18LT1090G Covered Rope Lay Braid

By Burndy
Catalog # [CCY10L18LT1090G](#)



Covered Rope Lay Braid.

Features

- Most Burndy braid are UL Listed and CSA Certified
- Pressed seamless copper ferrules provide added durability and prevent fraying, providing extra strength for a robust bonding connection
- Braid is especially suited for applications that require flexibility or resistance to vibration
- Extra fine stranding gives enhanced flexibility
- Ferrules clearly marked with Burndy braid type and UL markings (where appropriate)
- Available in custom lengths and hole sizes to suit your needs (contact your local sales representative for non-standard configurations)
- For assistance in finding the perfect braid for your needs click [here](#) for our Braid Configurator Tool:
www.hubbell.com/config/BRAID

General

Catalog Number	CCY10L18LT1090G
Connector Type	Rope lay
Material	Copper
UPC	781810674338
UPC 12 Digit	7818106743388

Dimensions

Dimension - L Length Overall	457.2 mm
mm	
Dimension - Length Overall	18.00 in
inch	
Length	18 in

Certifications And Compliance

Certification - CSA Approved	No
Standards - RoHS Compliance	CM
Status	

Logistics

Carton Quantity	50
Minimum Pack Quantity	1
Pallet Quantity	4800

Product Assets

[Catalogs - BURNDY Master Catalog - Section E2 - Mechanical Grounding](#)
[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
[Customer Notices - Prop 65 Notice](#)
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
[Sales Drawings - 50053133](#)
[Specifications - CCY10L18LT1090G](#)



A Hubbell brand