

CCY10L7G2 Rope Lay Braid

By Burndy

Catalog # [CCY10L7G2](#)

Rope Lay Braid.



Features

- Most Burndy braid are UL Listed and CSA Certified
- Pressed seamless copper ferrules provide added durability and prevent fraying, providing extra strength for a robust bonding connection
- Braid is especially suited for applications that require flexibility or resistance to vibration
- Extra fine stranding gives enhanced flexibility
- Ferrules clearly marked with Burndy braid type and UL markings (where appropriate)
- Available in custom lengths and hole sizes to suit your needs (contact your local sales representative for non-standard configurations)
- For assistance in finding the perfect braid for your needs click here for our Braid Configurator Tool: www.hubbell.com/config/BRAID

General

Catalog Number	CCY10L7G2
Connector Type	Rope lay
Material	Copper
UPC	781810543597
UPC 12 Digit	7818105435977

Dimensions

Dimension - L Length Overall	190.5 mm
mm	

Dimension - Length Overall	7.50 in
inch	
Length	7 in

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance	CM
Status	
UL Listed	No

Logistics

Carton Quantity	50
Minimum Pack Quantity	100
Pallet Quantity	12000

Product Assets

- [3D Models - CCY10L7G2_MODEL-PDF](#)
- [3D Models - CY14L24G6_MODEL-STEP](#)
- [3D Models - CCY10L7G2_MODEL-IGES](#)
- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Sales Drawings - 30026622](#)
- [Specifications - CCY10L7G2](#)