



# CCY10L9LT14GY Covered Rope Lay Braid

By Burndy  
Catalog # [CCY10L9LT14GY](#)

Covered Rope Lay Braid.



### Features

- Most Burndy braid are UL Listed and CSA Certified
- Pressed seamless copper ferrules provide added durability and prevent fraying, providing extra strength for a robust bonding connection
- Braid is especially suited for applications that require flexibility or resistance to vibration
- Extra fine stranding gives enhanced flexibility
- Ferrules clearly marked with Burndy braid type and UL markings (where appropriate)
- Available in custom lengths and hole sizes to suit your needs (contact your local sales representative for non-standard configurations)
- For assistance in finding the perfect braid for your needs click [here](#) for our Braid Configurator Tool:  
[www.hubbell.com/config/BRAID](http://www.hubbell.com/config/BRAID)

### General

Catalog Number	CCY10L9LT14GY
Connector Type	Rope lay
Material	Copper
UPC	781810674598
UPC 12 Digit	7818106745988

### Dimensions

Dimension - L Length Overall	240.28 mm
mm	
Dimension - Length Overall	9.46 in
inch	
Length	9 in

### Certifications And Compliance

Certification - CSA Approved	No
Standards - RoHS Compliance	CM
Status	

### Logistics

Carton Quantity	50
Minimum Pack Quantity	1
Pallet Quantity	12000

### Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)  
[Customer Notices - Prop 65 Notice](#)  
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)  
[Sales Drawings - 50048718](#)  
[Specifications - CCY10L9LT14GY](#)