



CCY6L24LT10B Covered Rope Lay Braid

By Burndy
Catalog # [CCY6L24LT10B](#)

Covered Rope Lay Braid.



Features

- Most Burndy braid are UL Listed and CSA Certified
- Pressed seamless copper ferrules provide added durability and prevent fraying, providing extra strength for a robust bonding connection
- Braid is especially suited for applications that require flexibility or resistance to vibration
- Extra fine stranding gives enhanced flexibility
- Ferrules clearly marked with Burndy braid type and UL markings (where appropriate)
- Available in custom lengths and hole sizes to suit your needs (contact your local sales representative for non-standard configurations)
- For assistance in finding the perfect braid for your needs click [here](#) for our Braid Configurator Tool:
www.hubbell.com/config/BRAID

General

Catalog Number CCY6L24LT10B
Connector Type Rope lay

| | |
|--------------|---------------|
| Material | Copper |
| UPC | 781810674666 |
| UPC 12 Digit | 7818106746666 |

Dimensions

| | |
|--------|-------|
| Length | 24 in |
|--------|-------|

Certifications And Compliance

| | |
|------------------------------|----|
| Certification - CSA Approved | No |
| Standards - RoHS Compliance | UI |
| Status | |

Logistics

| | |
|-----------------------|---|
| Minimum Pack Quantity | 1 |
|-----------------------|---|

Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
[Specifications - CCY6L24LT10B](#)