



CFDFR, Black Cover, Flame retardant cover for YH2929, 250 kcmil H-Tap

By Burndy
Catalog # [CFDFR](#)



H-Tap CRIMPIT™ Cover; Flame Retardant; 250 kcmil Max Conductor, 0.95" Max Connector Length.

Application

- Cover

General

Color	• Black
Color Code	Purple
Connector Type	H-TAP COVERS BLACK
EU RoHS Indicator	Yes
Fire Resistance	Yes
Insulation	Y
Material	POLYCARBONATE
Operating Temperature	90 °C
Plated	N
Plating Type	Unplated
Sub Brand	CRIMPIT
Temperature Rating	194
Trade Name	CRIMPIT™
Type	<ul style="list-style-type: none"> CF-FR, Flame Retardant CF-FR, Flame Retardant
UPC	781810132395
UPC 12 Digit	7818101323955

Dimensions

Dimension - Height inch	2.02 in
Dimension - L Length Overall mm	86 mm
Dimension - Length Overall inch	3.39 in
Dimension - Maximum Conductor Size Accommodated	250 kcmil
Dimension - Width inch	1.59 in
Thickness	0.08 in

Electrical Ratings

Voltage - Maximum	35000
Voltage Rating	600 V

Conductor Related

Conductor - AL Str Size	250 KCMIL
Conductor - Copper Str Compact Size	250 KCMIL
Conductor - Copper Str Size	250 KCMIL
Conductor - Copper Str Size Range	250 kcmil
Conductor - Material	COPPER
Conductor - Max Length	0.95 in
Conductor Type	CODE/FLEX
Wire Size	250 KCMIL

Certifications And Compliance

Certification - 94V0 Rated	N
Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Carton Quantity	25
Minimum Pack Quantity	1
Pallet Quantity	3600

Product Assets

- [3D Models - CFDFR_MODEL-IGES](#)
- [3D Models - CFDFR_MODEL-PDF](#)
- [3D Models - CFDFR_MODEL-STEP](#)
- [Catalogs - Full Line BURNDY Catalog](#)
- [Customer Notices - Prop 65 Notice](#)
- [Product Cross Section Image\(s\) - BUR_CFD_LineArt](#)
- [Sales Drawings - SD208803-01_1](#)



A proud member of the Hubbell Family.

