

CFOFR, Black Cover, Flame retardant cover for YH292C or YHYH298C, 250 kcmil H-Tap



By Burndy
Catalog # CFOFR

H Tap Flame Retardent Cover, 2 AWG Max Conductor, 0.80" Max Connector Length.

Application

Cover

General

Catalog Number	CFOFR
Color	Black
Color Code	Brown
Connector Type	H-TAP COVERS BLACK
EU RoHS Indicator	Yes
Fire Resistance	Yes
Insulation	Y
Material	POLYCARBONATE
Operating Temperature	90 °C
Plated	N
Plating Type	Unplated
Sub Brand	CRIMPIT
Temperature Rating	194
Trade Name	CRIMPIT™
Type	CF-FR, Flame Retardant
UPC	781810132388
UPC 12 Digit	7818101323888

Dimensions

Dimension - Height inch	1.90 in
Dimension - L Length Overall mm	86 mm
Dimension - Length Overall inch	3.39 in
Dimension - Maximum Conductor Size Accommodated	2 AWG
Dimension - Width inch Thickness	1.49 in 0.08 in

Electrical Ratings

Voltage - Maximum	35000
Voltage Rating	600 V

Conductor Related

Conductor - AL Str Size	2 AWG
Conductor - Copper Str	2 AWG
Compact Size	
Conductor - Copper Str Size	2 AWG
Conductor - Copper Str Size Range	#2 AWG
Conductor - Material	COPPER
Conductor - Max Length	0.80 in
Conductor Type	CODE/FLEX
Wire Size	2 AWG

Certifications And Compliance

Buy American Compliant	Yes
Certification - 94V0 Rated	N
Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Carton Quantity	25
Minimum Pack Quantity	1
Pallet Quantity	3600

Product Assets

- [3D Models - CFOFR_MODEL-STEP](#)
- [3D Models - CFOFR_MODEL-PDF](#)
- [3D Models - CFOFR_MODEL-IGES](#)
- [Catalogs - BURNDY Master Catalog - Section C - Compression Connections](#)
- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Product Cross Section Image\(s\) - BUR_CFO_LineArt](#)
- [Sales Drawings - SD208803-01_1](#)
- [Specifications - CFOFR](#)



A Hubbell brand