



CH10M, Cable Tie Hanger

By Burndy
Catalog # [CH10M](#)



Nylon Cable Hanger.

Features

- Cable hangers provide a contact area range of 1/2" to 3/8" in width
- All contact edges have a full radius for product protection
- Sizes clearly marked on each clamp

General

Color	Natural
Material	NYLON 6/6
Mounting Method	Screw
Trade Name	UNIRAP™
UPC	781810336410

Dimensions

Dimension - Bundle Diameter Max inch	0.62
Dimension - Width inch	0.38 in
Dimension - Width mm	10 mm

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - UV Rated	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Minimum Pack Quantity	5000
Packaging Type	Bag

Product Assets

[Catalogs - Full Line BURNDY Catalog](#)
[Product Cross Section Image\(s\) - BUR_CH_CABLE_HANGERS_LineArt](#)
[Sales Drawings - 50042701](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
BRDY-CH10M-SPEC-EN | REV 6/2024