

## CH11M, Cable Tie Hanger

By Burndy  
Catalog # [CH11M](#)

Nylon Cable Hanger.



### Features

- Cable hangers provide a contact area range of 1/2" to 3/8" in width
- All contact edges have a full radius for product protection
- Sizes clearly marked on each clamp

### General

Catalog Number	CH11M
Color	Natural
Material	NYLON 6/6
Mounting Method	Screw
UPC	781810336458

### Dimensions

Dimension - Bundle Diameter Max inch	0.62
Dimension - Width inch	0.5
Dimension - Width mm	13 mm

### Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - UV Rated	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

### Logistics

Carton Quantity	1000
Minimum Pack Quantity	5000
Packaging Type	Bag

### Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)  
[Catalogs - BURNDY Master Catalog - Section G - Wire Management](#)  
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)  
[Product Cross Section Image\(s\) - BUR\\_CH\\_CABLE\\_HANGERS\\_LineArt](#)  
[Sales Drawings - 50080809](#)  
[Specifications - CH11M](#)