



CH11M, Cable Tie Hanger

By Burndy
Catalog # [CH11M](#)

Nylon Cable Hanger.



Features

- Cable hangers provide a contact area range of 1/2" to 3/8" in width
- All contact edges have a full radius for product protection
- Sizes clearly marked on each clamp

General

Catalog Number	CH11M
Color	Natural
Material	NYLON 6/6
Mounting Method	Screw
UPC	781810336458

Dimensions

Dimension - Bundle Diameter Max inch	0.62
Dimension - Width inch	0.5
Dimension - Width mm	13 mm

Certifications And Compliance

Certification - CSA Approved	No
------------------------------	----

Certification - ETL	No
Certification - UL Recognized	No
Certification - UV Rated	No
Certification - cULus	No
Standards - RoHS Compliance	CM
Status	
UL Listed	No

Logistics

Carton Quantity	1000
Minimum Pack Quantity	5000
Packaging Type	Bag

Product Assets

- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Catalogs - BURNDY Master Catalog - Section G - Wire Management](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Product Cross Section Image\(s\) - BUR_CH_CABLE_HANGERS_LineArt](#)
- [Sales Drawings - 50080809](#)
- [Specifications - CH11M](#)