

CH12M0, Cable Tie Hanger

By Burndy
Catalog # [CH12M0](#)

Nylon Cable Hanger.



Features

- Cable hangers provide a contact area range of 1/2" to 3/8" in width
- All contact edges have a full radius for product protection
- Sizes clearly marked on each clamp

General

Catalog Number	CH12M0
Color	Black
Material	NYLON 6/6
Mounting Method	Screw
UPC	781810336502

Dimensions

Dimension - Bundle Diameter Max inch	0.75
Dimension - Width inch	0.50 in
Dimension - Width mm	13 mm

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - UV Rated	Yes
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Carton Quantity	1000
Minimum Pack Quantity	3000
Packaging Type	Bag

Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
[Catalogs - BURNDY Master Catalog - Section G - Wire Management](#)
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
[Product Cross Section Image\(s\) - BUR_CH_CABLE_HANGERS_LineArt](#)
[Sales Drawings - 50080809](#)
[Specifications - CH12M0](#)