



## CH24L, Cable Tie Hanger

By Burndy  
Catalog # [CH24L](#)

Nylon Cable Hanger.



### Features

- Cable hangers provide a contact area range of 1/2" to 3/8" in width
- All contact edges have a full radius for product protection
- Sizes clearly marked on each clamp

### General

Catalog Number	CH24L
Color	Natural
Material	NYLON 6/6
Mounting Method	Screw
UPC	781810336670

### Dimensions

Dimension - Bundle Diameter Max inch	1.65
Dimension - Width inch	0.49
Dimension - Width mm	12 mm

### Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - UV Rated	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

### Logistics

Carton Quantity	1000
Minimum Pack Quantity	1000
Packaging Type	Bag

### Product Assets

- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Catalogs - BURNDY Master Catalog - Section G - Wire Management](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Product Cross Section Image\(s\) - BUR\\_CH\\_CABLE\\_HANGERS\\_LineArt](#)
- [Sales Drawings - 50080809](#)
- [Specifications - CH24L](#)