

CH4M, Cable Tie Hanger

By Burndy
Catalog # CH4M

Nylon Cable Hanger.



Features

- Cable hangers provide a contact area range of 1/2" to 3/8" in width
- All contact edges have a full radius for product protection
- Sizes clearly marked on each clamp

General

| | |
|-----------------|--------------|
| Catalog Number | CH4M |
| Color | Natural |
| Material | NYLON 6/6 |
| Mounting Method | Screw |
| Trade Name | UNIRAP™ |
| UPC | 781810336175 |

Dimensions

| | |
|---|-------|
| Dimension - Bundle Diameter Max inch | .27 |
| Dimension - Width inch | 0.4 |
| Dimension - Width mm | 10 mm |

Certifications And Compliance

| | |
|---------------------------------------|----|
| Certification - CSA Approved | No |
| Certification - ETL | No |
| Certification - UL Recognized | No |
| Certification - UV Rated | No |
| Certification - cULus | No |
| Standards - RoHS Compliance Status | CM |
| UL Listed | No |

Logistics

| | |
|-----------------------|------|
| Carton Quantity | 1000 |
| Minimum Pack Quantity | 5000 |
| Packaging Type | Bag |

Product Assets

- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Catalogs - BURNDY Master Catalog - Section G - Wire Management](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Product Cross Section Image\(s\) - BUR_CH_CABLE_HANGERS_LineArt](#)
- [Sales Drawings - 50080809](#)
- [Specifications - CH4M](#)