

CH8M, Cable Tie Hanger

By Burndy
Catalog # [CH8M](#)



Nylon Cable Hanger.

Features

- Cable hangers provide a contact area range of 1/2" to 3/8" in width
- All contact edges have a full radius for product protection
- Sizes clearly marked on each clamp

General

Catalog Number	CH8M
Color	Natural
Material	NYLON 6/6
Mounting Method	Screw
Trade Name	UNIRAP™
UPC	781810336335

Dimensions

Dimension - Bundle Diameter Max inch	.54
Dimension - Width inch	0.48
Dimension - Width mm	12 mm

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - UV Rated	No
Certification - cULus	No
Standards - RoHS Compliance	CM
Status	
UL Listed	No

Logistics

Carton Quantity	1000
Minimum Pack Quantity	5000
Packaging Type	Bag

Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
[Catalogs - BURNDY Master Catalog - Section G - Wire Management](#)
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
[Product Cross Section Image\(s\) - BUR_CH_CABLE_HANGERS_LineArt](#)
[Sales Drawings - 50080809](#)
[Specifications - CH8M](#)