



CKSU22, 1 KSU22 Universal Split Bolt packaged with SC2 Cover

By Burndy
Catalog # [CKSU22](#)

Universal SERVIT W/SC2 Cover Accom: Equal Run & Tap: 10 SOL-2 SOL UL Listed For Cu Only Torque: 275 lb-in Metric Range: 6mm-25mm, TRQ: 31Nm.



General

Connector Type	Split Bolt
Material	Copper
Plated	Y
Plating Type	Tin - Electro Plated
Trade Name	SERVIT®
UPC	781810294901
UPC 12 Digit	7818102949011

Conductor Related

Conductor Type	<ul style="list-style-type: none">• CU C Solid-Run• CU C Str-Run• AL C Str-Run• AAAC C 5005-Run• AAAC C 6201-Run• ACSR C Str-Run• CU C Solid-Tap• CU C Str-Tap• AL C Str-Tap• AAAC C 5005-Tap• AAAC C 6201-Tap• ACSR C Str-Tap• GAL Steel C Str-Size
----------------	--

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Carton Quantity	25
Minimum Pack Quantity	25
Pallet Quantity	3600

Product Assets

[Catalogs - Full Line BURNDY Catalog](#)
[Customer Notices - Prop 65 Notice](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
BRDY-CKSU22-SPEC-EN | REV 5/2024