



# CL1/014TN, Copper Lay-in Lug, Tin Plated

By Burndy  
Catalog # [CL1/014TN](#)



COPPER LAY-IN-LUG WIRE RANGE: 1/0 - 14 STEEL SET SCREW  
TIN PLATED.

### Features

- UL Listed for Grounding
- CSA Certified
- Suitable for copper conductors only

### General

Catalog Number	CL1/014TN
Plated	Y
Plating Type	Tin
Trade Name	QIKLUG™
UPC	781810505144
UPC 14 Digit GTIN	00781810505144

### Dimensions

Dimension - Height inch	1.17 in
Dimension - Hole Size inch	0.27 in
Dimension - Length Overall inch	1.50 in
Dimension - Pad Width inch	0.60 in
Dimension - Width inch	0.60 in

### Conductor Related

Conductor - Copper Solid Size	14 AWG;13 AWG;12 AWG;11 AWG;10 AWG;9 AWG;8 AWG;7 AWG;6 AWG;5 AWG;4 AWG;3 AWG;2 AWG;1 AWG;1/0 AWG
Conductor - Copper Solid Size Range	14 AWG-1/0 AWG

Conductor - Copper Str Size	14 AWG;12 AWG;10 AWG;9 AWG;8 AWG;7 AWG;6 AWG;5 AWG;4 AWG;3 AWG;2 AWG;1 AWG;1/0
Conductor - Copper Str Size Range	14 AWG - 1/0 AWG

### Certifications And Compliance

Buy America(n) Qualified	Contact Manufacturer
Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance	CM
Status	
UL Listed	Yes

### Logistics

Carton Quantity	240
Minimum Pack Quantity	1

### Product Assets

- [Catalogs - BURNDY Master Catalog - Section A - Mechanical](#)
- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Product Cross Section Image\(s\) - BUR\\_CL\\_LA](#)
- [Sales Drawings - 30000650](#)
- [Specifications - CL1014TN](#)



A Hubbell brand