

CL501TNBULK, Copper Lay-in Lug

By Burndy
Catalog # [CL501TNBULK](#)



QIKLUG, LAY-IN LUG - BULK VERSION 14-10 AWG20 lb-in
Torque 8 AWG25 lb-in Torque 6-4 AWG35 lb-in Torque.

Features

- UL2703 for Solar Applications
- UL467 for Direct Burial

General

Catalog Number	CL501TNBULK
Material	Copper
Material - Hardware	Stainless Steel
Plated	Y
Plating Type	Tin
Trade Name	QIKLUG™
UPC	781810492796
UPC 14 Digit GTIN	00781810492796

Dimensions

Dimension - D inch	0.47 in
Dimension - Height inch	0.85 in
Dimension - Hole Size inch	0.22 in
Dimension - Length Overall inch	1.13 in
Dimension - N inch	0.19 in
Dimension - Stud Size inch	17/64
Dimension - Width inch	0.38 in

Conductor Related

Conductor - Copper Str Size	14 AWG;12 AWG;10 AWG;9 AWG;8 AWG;7 AWG;6 AWG;5 AWG;4 AWG
-----------------------------	--

Conductor - Copper Str Size Range	14 AWG - 4 AWG
-----------------------------------	----------------

Certifications And Compliance

Buy America(n) Qualified	Contact Manufacturer
Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Listed Direct Burial	Yes
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Carton Quantity	500
Minimum Pack Quantity	500

Product Assets

[3D Models - CL501TNBULK_MODEL-IGES](#)
[3D Models - CL501TNBULK_MODEL-PDF](#)
[3D Models - CL501TNBULK_MODEL-STEP](#)
[Catalogs - Burndy Grounding Catalog](#)
[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
[Product Cross Section Image\(s\) - BUR_CL501_LineArt](#)
[Sales Drawings - SC212515-01](#)
[Specifications - CL501TNBULK](#)

