



CP2525, Heavy Duty Parallel Connector, Copper, A=1/0 Str, B=1/0 Str

By Burndy
Catalog # [CP2525](#)



GROOVE A: 1/0 STR CU GROOVE B: 1/0 STR CU.

General

Material	Copper Alloy
Plated	N
Plating Type	Unplated
UPC	781810012833
UPC 12 Digit	7818100128333

Dimensions

Dimension - B Length fraction	3 in
Dimension - B Length inch	3 in
Dimension - Height inch	13/16 in
Dimension - Width fraction	1-5/8 in
Dimension - Width inch	1 9/16 in

Conductor Related

Conductor - Copper Str Size A	1/0
Conductor - Copper Str Size A Range	1/0
Conductor - Copper Str Size B	1/0
Conductor - Copper Str Size B Range	1/0

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	EX
UL Listed	No

Logistics

Minimum Pack Quantity	1
-----------------------	---

Product Assets

[Catalogs - Full Line BURNDY Catalog](#)
[Customer Notices - Prop 65 Notice](#)
[Product Cross Section Image\(s\) - BUR_CP_LineArt](#)
[Sales Drawings - SA008893-01](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
BRDY-CP2525-SPEC-EN | REV 5/2024