



CP25A25A, Aluminum Alloy Connector for Tap or Parallel Connections

By Burndy
Catalog # [CP25A25A](#)



High strength, high conductivity aluminum body and hardware provide corrosion resistant assembly. Recommended for tap or parallel connections.

General

Installation Torque Recommended in-lb	300 LBS/in
Material	Aluminum
Plated	N
Plating Type	Unplated
UPC	781810012956
UPC 12 Digit	7818100129566

Dimensions

Dimension - B Length inch	3.25 in
Dimension - Height inch	2.32 in
Dimension - Width inch	1.56 in

Conductor Related

Conductor - ACSR Str Size Range	1/0 (6/1) AWG
Conductor - ACSR Str Tap Range	1 AWG - 80 mm ²
Conductor - AL Str Size	1/0 AWG
Conductor - Copper Str Size	1/0 AWG

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Minimum Pack Quantity	1
-----------------------	---

Product Assets

[Catalogs - Full Line BURNDY Catalog](#)
[Customer Notices - Prop 65 Notice](#)
[Product Cross Section Image\(s\) - BUR_CPA_CLAMP_LineArt](#)
[Sales Drawings - SD..028518-01](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
BRDY-CP25A25A-SPEC-EN | REV 5/2024