

# CP26A26A, Aluminum Alloy Connector for Tap or Parallel Connections

By Burndy  
Catalog # [CP26A26A](#)



ACSR, 6201, 5005: 1/0 CU. & ALUM.: 3/0 SOL - 2/0 STR.  
GROOVE A GROOVE B.

## Features

- Cast Aluminum Parallel Groove Clamp with Aluminum Hardware
- Recommended for tap or parallel connections
- High strength, high conductivity
- Long contact surface for excellent contact and full conductivity
- PENETROX™ joint compound recommended for all combinations

## General

Catalog Number	CP26A26A
Material	Aluminum
Plated	N
Plating Type	Unplated
UPC	781810012963
UPC 12 Digit	7818100129633

## Dimensions

Dimension - B Length inch	4 in
Dimension - Height fraction	2-7/8 in
Dimension - Height inch	2.875 in
Dimension - Height mm	73 mm
Dimension - Width fraction	2-1/8 in
Dimension - Width inch	2.09 in
Dimension - Width mm	54 mm

## Conductor Related

Conductor - ACSR Str Size	6 (6/1) Turkey AWG
Conductor - ACSR Str Size Range	6 (6/1) Turkey AWG
Conductor - AL Str Size A	2/0 AWG;3/0 AWG

Conductor - AL Str Size A Range	2/0 AWG-3/0 AWG
Conductor - AL Str Size B	2/0 AWG;3/0 AWG
Conductor - AL Str Size B Range	2/0 AWG-3/0 AWG
Conductor - Copper Str Size A	2/0 AWG;3/0 AWG
Conductor - Copper Str Size A Range	2/0 AWG-3/0 AWG
Conductor - Copper Str Size B	2/0 AWG;3/0 AWG
Conductor - Copper Str Size B Range	2/0 AWG-3/0 AWG

## Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

## Logistics

Minimum Pack Quantity	10
-----------------------	----

## Product Assets

- [Catalogs - BURNDY Master Catalog - Section H - Overhead Distribution](#)
- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Product Cross Section Image\(s\) - BUR\\_CPA\\_LineArt](#)
- [Sales Drawings - 28518](#)
- [Specifications - CP26A26A](#)