

CP28A28A, Aluminum Alloy Connector for Tap or Parallel Connections

By Burndy
Catalog # [CP28A28A](#)



ACSR,6201,5005: 3/0, 134.6(12-7) CU.& ALUM.: 4/0 STR.
GROOVE A GROOVE B.

Features

- Cast Aluminum Parallel Groove Clamp with Aluminum Hardware
- Recommended for tap or parallel connections
- High strength, high conductivity
- Long contact surface for excellent contact and full conductivity
- PENETROX™ joint compound recommended for all combinations

General

Catalog Number	CP28A28A
Installation Torque	300 LBS/in
Recommended in-lb	
Material	Aluminum
Plated	N
Plating Type	Unplated
UPC	781810012994
UPC 12 Digit	7818100129944

Dimensions

Dimension - B Length inch	4 in
Dimension - Height fraction	2-7/8 in
Dimension - Height inch	2.875 in
Dimension - Width fraction	2-1/8 in
Dimension - Width inch	2.09 in
Dimension - Width mm	54 mm

Conductor Related

Conductor - ACSR Str Size	134.6 (12/7) Leghorn kcmil
Conductor - ACSR Str Size Range	134.6 (12/7) Leghorn kcmil
Conductor - AL Str Size A	4/0 AWG
Conductor - AL Str Size A Range	4/0 AWG
Conductor - AL Str Size B	4/0 AWG
Conductor - AL Str Size B Range	4/0 AWG
Conductor - Copper Str Size A	4/0 AWG
Conductor - Copper Str Size A Range	4/0 AWG
Conductor - Copper Str Size B	4/0 AWG
Conductor - Copper Str Size B Range	4/0 AWG

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Minimum Pack Quantity	10
-----------------------	----

Product Assets

- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Catalogs - BURNDY Master Catalog - Section H - Overhead Distribution](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Product Cross Section Image\(s\) - BUR_CPA_CLAMP_LineArt](#)
- [Sales Drawings - SD..028518-01](#)
- [Specifications - CP28A28A](#)



A Hubbell brand