

CP2928, Heavy Duty Parallel Connector, Copper, A=250 kcmil, B=4/0 Str

By Burndy
Catalog # [CP2928](#)



Accom: Groove A: 250 kcmil Cu Groove B: 4/0 STR Cu.

Features

- High strength, high copper alloy
- Recommended for heavy duty parallel connections
- Silicon bronze hardware and cast copper body provides corrosion resistant assembly
- Long contact surface provides excellent full conductivity

General

Catalog Number	CP2928
Material	Copper Alloy
Plated	N
Plating Type	Unplated
UPC	781810455838
UPC 12 Digit	7818104558388

Dimensions

Dimension - B Length inch	4 in
Dimension - Height inch	1 1/16 in
Dimension - Height mm	0 mm
Dimension - Width inch	1 15/16 in

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	EX
UL Listed	No

Logistics

Minimum Pack Quantity	6
-----------------------	---

Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
[Customer Notices - Prop 65 Notice](#)
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
[Product Cross Section Image\(s\) - BUR_CP_LineArt](#)
[Sales Drawings - SA008893-01](#)
[Specifications - CP2928](#)