

## CP36A36A, Aluminum Alloy Connector for Tap or Parallel Connections

By Burndy

Catalog # [CP36A36A](#)



CABLE GROOVE A AL. - CU 600 ACS GROOVE B AL.-CU 600 ACS.

### Features

- Cast Aluminum Parallel Groove Clamp with Aluminum Hardware
- Recommended for tap or parallel connections
- High strength, high conductivity
- Long contact surface for excellent contact and full conductivity
- PENETROX™ joint compound recommended for all combinations

### General

Catalog Number	CP36A36A
Installation Torque	300 LBS/in
Recommended in-lb	
Material	Aluminum
Plated	N
Plating Type	Unplated
UPC	781810080986
UPC 12 Digit	7818100809866

### Dimensions

Dimension - Length Overall	5.25
inch	

### Conductor Related

Conductor - ACSR Str Size	477 kcmil
Conductor - AL Str Size Range	550 kcmil - 600 kcmil

### Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance	CM
Status	
UL Listed	No

### Logistics

Minimum Pack Quantity	6
-----------------------	---

### Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)  
[Customer Notices - Prop 65 Notice](#)  
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)  
[Product Cross Section Image\(s\) - BUR\\_CPA\\_CLAMP\\_LineArt](#)  
[Sales Drawings - SD..028518-01](#)  
[Specifications - CP36A36A](#)