



CP4444, Heavy Duty Parallel Connector, Copper, A=1000 kcmil, B=1000 kcmil

By Burndy
Catalog # [CP4444](#)



Copper Alloy Heavy Duty Parallel Connector accommodates 1000 kcmil.

Features

- High strength, high copper alloy
- Recommended for heavy duty parallel connections
- Silicon bronze hardware and cast copper body provides corrosion resistant assembly
- Long contact surface provides excellent full conductivity

General

Catalog Number	CP4444
Material	Copper Alloy
Plated	N
Plating Type	Unplated
UPC	781810246689
UPC 12 Digit	7818102466899

Dimensions

Dimension - Height mm	0 mm
Dimension - Length Overall inch	5

Conductor Related

Conductor - AL Str Size 1000 kcmil

Certifications And Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Minimum Pack Quantity 4

Product Assets

- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Customer Notices - Prop 65 Notice](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Product Cross Section Image\(s\) - BUR_CP_LineArt](#)
- [Sales Drawings - SA..005802-01](#)
- [Specifications - CP4444](#)