



CSB037800SR1, Cold Shrink Splice Kit, Black, Conductor Range: #2-1/0 AWG

By Burndy
Catalog # [CSB037800SR1](#)

Cold Shrink Splice,Black ,Conductor Range: #2-1/0,Relaxed Tube Length: 8",App. Range: 0.37-0.84.



Features

- Easy, safe installation
- Suitable for a wide range of cable sizes
- UV resistance, thermal stability
- No special tools or training required
- Forms a moisture proof seal
- Superior, time-saving insulation technology
- Indoor and outdoor applications

Application

Indoor and outdoor applications

General

Catalog Number	CSB037800SR1
Color	Black
Connector Type	SEAL SPLICE KITS
EU RoHS Indicator	Yes
Material	RUBBER
Sub Brand	COLD SHRINK SPLICE
Type	CSB
UPC	621945441590

Conductor Related

Conductor Size 2AWG - 1/0AWG

Certifications And Compliance

Buy American Compliant	No
Certification - CSA Approved	No
Standards - RoHS Compliance Status	CM

Logistics

Minimum Pack Quantity 1

Product Assets

- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Catalogs - Cable Accessories](#)
- [Catalogs - BURNDY Master Catalog - Section D - Shrink Tubing](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Sales Drawings - 50057035](#)
- [SDS - Cold Seal Splice Kit Part A SDS](#)
- [Specifications - CSB037800SR1](#)
- [Video - Grease Best PRactices](#)



A Hubbell brand