



## CSB051900SR1, Cold Shrink Splice Kit, Black, Conductor Range: 2/0-400 kcmil

By Burndy

Catalog # [CSB051900SR1](#)

In-line splice sealing kit, Conductor range- 2/0-400, Supplied tube length- 7.5", Relaxed tube length- 9.00".



### Features

- Easy, safe installation
- Suitable for a wide range of cable sizes
- UV resistance, thermal stability
- No special tools or training required
- Forms a moisture proof seal
- Superior, time-saving insulation technology
- Indoor and outdoor applications

### General

Catalog Number	CSB051900SR1
Connector Type	SEAL SPLICE KITS
Material	RUBBER
UPC	621945441965

### Dimensions

Dimension - Height mm	0 mm
-----------------------	------

### Conductor Related

Conductor Size 2/0AWG - 400kcmil

### Certifications And Compliance

Certification - CSA Approved No  
Standards - RoHS Compliance CM  
Status

### Logistics

Minimum Pack Quantity 1

### Product Assets

[Catalogs - BURNDY Master Catalog - Section D - Shrink Tubing](#)  
[Catalogs - Cable Accessories](#)  
[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)  
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)  
[Sales Drawings - 50057035](#)  
[SDS - Cold Seal Splice Kit Part A SDS](#)  
[Specifications - CSB051900SR1](#)  
[Video - Grease Best Practices](#)