

CSB0971200SR1, Cold Seal Splice Kit, Forms a moisture proof seal

By Burndy
Catalog # CSB0971200SR1



In-line splice sealing kit, Conductor range- 500-800, Supplied tube length- 10.5", Relaxed tube length- 12.00".

Features

- Easy, safe installation
- Suitable for a wide range of cable sizes
- UV resistance, thermal stability
- No special tools or training required
- Forms a moisture proof seal
- Superior, time-saving insulation technology
- Indoor and outdoor applications

General

Catalog Number	CSB0971200SR1
Connector Type	SEAL SPLICE KITS
Material	RUBBER
UPC	621945441989

Dimensions

Dimension - Height mm	0 mm
-----------------------	------

Conductor Related

Conductor Size	500kcmil - 800kcmil
----------------	---------------------

Certifications And Compliance

Certification - CSA Approved	No
Standards - RoHS Compliance	CM
Status	

Logistics

Minimum Pack Quantity	1
-----------------------	---

Product Assets

- [Catalogs - BURNDY Master Catalog - Section D - Shrink Tubing](#)
- [Catalogs - Cable Accessories](#)
- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Sales Drawings - 50057035](#)
- [SDS - Cold Seal Splice Kit Part A SDS](#)
- [Specifications - CSB0971200SR1](#)
- [Video - Grease Best PRactices](#)