



## CSB125900SR1, Cold Shrink Splice Kit, Black, Conductor Range: 900-1000 kcmil

By Burndy

Catalog # [CSB125900SR1](#)

In-line splice sealing kit, Conductor range- 900-100, Supplied tube length- 7.5", Relaxed tube length- 9.00".



### Features

- Easy, safe installation
- Suitable for a wide range of cable sizes
- UV resistance, thermal stability
- No special tools or training required
- Forms a moisture proof seal
- Superior, time-saving insulation technology
- Indoor and outdoor applications

### General

Catalog Number	CSB125900SR1
Connector Type	SEAL SPLICE KITS
Material	RUBBER
UPC	621945441996

### Dimensions

Dimension - Height mm	0 mm
-----------------------	------

### Conductor Related

Conductor Size	900kcmil - 1000kcmil
----------------	----------------------

### Certifications And Compliance

Certification - CSA Approved	No
Standards - RoHS Compliance Status	CM

### Logistics

Minimum Pack Quantity	1
-----------------------	---

### Product Assets

- [Catalogs - BURNDY Master Catalog - Section D - Shrink Tubing](#)
- [Catalogs - Cable Accessories](#)
- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Sales Drawings - 50057035](#)
- [SDS - Cold Seal Splice Kit Part A SDS](#)
- [Specifications - CSB125900SR1](#)
- [Video - Grease Best Practices](#)



A Hubbell brand