



CSUDO252810250J, Cold Shrink Med Volt Termination Kit, 25-28kV Utility, Jacketed Concentric Neutral Outdoor Sleeve Only

By Burndy
Catalog # CSUDO252810250J

Medium Voltage Cold Shrink Sleeve.



Features

- All-in-one integrated body incorporating stress control and sealant mastics
- Unique stress control system based on microvaristor (ZnO) technology that delivers exceptional discharge and impulse performance
- Quick and easy installation. Offering fewest number of steps to install
- Improved spiral rip core assembly uses smooth edges for simpler installation with less effort, heat tacked spiral core prevents unravelling during shipping and handling
- Excellent UV Resistance and hydrophobic characteristics
- Silicone Rubber body provides excellent track and erosion resistance

General

Boot Type	NO
Catalog Number	CSUDO252810250J
EU RoHS Indicator	Under Review
Environmental Conditions	Outdoor
Material	Caoutchouc de silicone
Pin Type	N/A
Series	UD-JCN
Terminal Type	N/A
UPC	621945584778

Electrical Ratings

Phase	1-Phase
Voltage Rating	25/28 kV

Conductor Related

Conductor Range	<ul style="list-style-type: none">• 5-8kV: 350-750 kcmil• 15kV: 4/0 AWG-500 kcmil• 25-28kV: 1/0 AWG-250 kcmil
-----------------	---

Certifications And Compliance

Buy American Compliant	Under Review
------------------------	--------------

Logistics

Carton Quantity	1
Pallet Quantity	72

Product Assets

- [Brochures - Cold Shrink Medium Voltage Cable Terminations Brochure](#)
- [Catalog Page - BURNDY MVColdShrinkTerminationKits CSUDO-B CSUDO-J CatCut](#)
- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Catalogs - BURNDY Master Catalog - Section D - Shrink Tubing](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Sales Drawings - 50095766-01](#)
- [Specifications - CSUDO252810250J](#)