



## CSUDO2528140J, Cold Shrink Med Volt Termination Kit, 25-28kV Utility, Jacketed Concentric Neutral Outdoor Sleeve Only

By Burndy  
Catalog # CSUDO2528140J

Medium Voltage Cold Shrink Sleeve.

### Features

- All-in-one integrated body incorporating stress control and sealant mastics
- Unique stress control system based on microvaristor (ZnO) technology that delivers exceptional discharge and impulse performance
- Quick and easy installation. Offering fewest number of steps to install
- Improved spiral rip core assembly uses smooth edges for simpler installation with less effort, heat tacked spiral core prevents unravelling during shipping and handling
- Excellent UV Resistance and hydrophobic characteristics
- Silicone Rubber body provides excellent track and erosion resistance

### General

Boot Type	NO
Catalog Number	CSUDO2528140J
EU RoHS Indicator	Under Review
Environmental Conditions	Outdoor
Material	Caoutchouc de silicone
Pin Type	N/A
Series	UD-JCN
Terminal Type	N/A
UPC	621945584761



### Electrical Ratings

Phase	1-Phase
Voltage Rating	25/28 kV

### Conductor Related

Conductor Range	<ul style="list-style-type: none"><li>• 5-8kV: 4/0 AWG-500 kcmil</li><li>• 15kV: 1/0 AWG-250 kcmil</li><li>• 25-28kV: #1-4/0 AWG</li></ul>
-----------------	--

### Certifications And Compliance

Buy American Compliant	Under Review
------------------------	--------------

### Logistics

Carton Quantity	1
Pallet Quantity	72

### Product Assets

- [Brochures - Cold Shrink Medium Voltage Cable Terminations Brochure](#)
- [Catalog Page - BURNDY MVColdShrinkTerminationKits CSUDO-B CSUDO-J CatCut](#)
- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Catalogs - BURNDY Master Catalog - Section D - Shrink Tubing](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Sales Drawings - 50095766-01](#)
- [Specifications - CSUDO2528140J](#)