



# CT110200SSBC0, Nylon Cable Tie, 110 lb Tensile Strength, Stainless Steel Barb, 8.7" Long, Black

By Burndy  
Catalog # [CT110200SSBC0](#)



Nylon Stainless Steel BARB Cable Ties, 8.7 IN L, .28 IN W, Tensile Strength: 110 Lbs,Material:Nylon 6/6.

## Features

Stainless Steel Barb Tie

## Application

For use with self-locking stainless steel barb

## General

Catalog Number	CT110200SSBC0
Color	Black
EU RoHS Indicator	Yes
Material	NYLON 6/6
Rating - Minimum Tensile Strength lbs	110 lb
Sub Brand	UNIRAP,CABLE TIE
Trade Name	UNIRAP™
Type	CT_SSB
UPC	781810564776

## Dimensions

Dimension - Bundle Diameter Max inch	2.01
Dimension - L Length Overall mm	221 mm

Dimension - Length Overall inch	8.70 in
Dimension - Width inch	0.28 in
Dimension - Width mm	7 mm

## Certifications And Compliance

Buy American Compliant	No
Certification - CSA Approved	Yes
Certification - ETL	No
Certification - cULus	Y
Standards - RoHS Compliance Status	CM

## Logistics

Carton Quantity	5000
Minimum Pack Quantity	100

## Product Assets

- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Catalogs - BURNDY Master Catalog - Section G - Wire Management](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Sales Drawings - 30022708](#)
- [Specifications - CT110200SSBC0](#)