



CT110325SSBC0, Nylon Cable Tie, 110 lb Tensile Strength, Stainless Steel Barb, 3.15" Bundle, Black

By Burndy
Catalog # CT110325SSBC0



Nylon 6/6 UV Stabilized Cable Tie with Stainless Steel Barb, 110 Lbs, UV Resistant Black, 3.15" Bundle Dia., Package: 100.

Features

Stainless Steel Barb Tie

Application

For use with self-locking stainless steel barb

General

Catalog Number	CT110325SSBC0
Color	Black
EU RoHS Indicator	Yes
Material	NYLON 6/6
Rating - Minimum Tensile Strength lbs	110 lb
Sub Brand	UNIRAP,CABLE TIE
Trade Name	UNIRAP™
Type	CT_SSB
UPC	781810564790

Dimensions

Dimension - Bundle Diameter Max inch	3.15
Dimension - L Length Overall mm	300 mm

Dimension - Length Overall inch	11.81
Dimension - Width inch	0.28
Dimension - Width mm	7

Certifications And Compliance

Buy American Compliant	No
Certification - CSA Approved	Yes
Certification - ETL	No
Certification - cULus	Y
Standards - RoHS Compliance Status	CM

Logistics

Carton Quantity	5000
Minimum Pack Quantity	100

Product Assets

- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Catalogs - BURNDY Master Catalog - Section G - Wire Management](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Sales Drawings - 30022708](#)
- [Specifications - CT110325SSBC0](#)