



## CT110500SSBLO, Nylon Cable Tie, 110 lb Tensile Strength, Stainless Steel Barb, 18.11" Long, Black

By Burndy  
Catalog # [CT110500SSBLO](#)

Nylon Stainless Steel BARB Cable Ties, 18.11 IN L, .28 IN W, Tensile Strength: 110 Lbs,Max bundle dia:5".



### Features

Stainless Steel Barb Tie

### Application

For use with self-locking stainless steel barb

### General

Catalog Number	CT110500SSBLO
Color	Black
EU RoHS Indicator	Yes
Material	NYLON 6/6
Rating - Minimum Tensile Strength lbs	110
Sub Brand	UNIRAP,CABLE TIE
Trade Name	UNIRAP™
Type	CT_SSB
UPC	781810565438

### Dimensions

Dimension - Bundle Diameter Max inch	5
Dimension - L Length Overall mm	460 mm
Dimension - Length Overall inch	18.11 in
Dimension - Width inch	0.28 in
Dimension - Width mm	7 mm

### Certifications And Compliance

Buy American Compliant	No
Certification - CSA Approved	Yes
Certification - ETL	No
Certification - cULus	Y
Standards - RoHS Compliance Status	CM

### Logistics

Carton Quantity	3000
Minimum Pack Quantity	50

### Product Assets

- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Catalogs - BURNDY Master Catalog - Section G - Wire Management](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Sales Drawings - 30022708](#)
- [Specifications - CT110500SSBLO](#)