



# CT110500SSBL0, Nylon Cable Tie, 110 lb Tensile Strength, Stainless Steel Barb, 18.11" Long, Black

By Burndy  
Catalog # [CT110500SSBL0](#)

Nylon Stainless Steel BARB Cable Ties, 18.11 IN L, .28 IN W,  
Tensile Strength: 110 Lbs,Max bundle dia:5".

## Features

Stainless Steel Barb Tie

## Application

For use with self-locking stainless steel barb

## General

Catalog Number	CT110500SSBL0
Color	Black
EU RoHS Indicator	Yes
Material	NYLON 6/6
Rating - Minimum Tensile Strength lbs	110
Sub Brand	UNIRAP,CABLE TIE
Trade Name	UNIRAP™
Type	CT_SSB
UPC	781810565438

## Dimensions

Dimension - Bundle Diameter Max inch	5
Dimension - L Length Overall mm	460 mm



Dimension - Length Overall inch	18.11 in
Dimension - Width inch	0.28 in
Dimension - Width mm	7 mm

## Certifications And Compliance

Buy American Compliant	No
Certification - CSA Approved	Yes
Certification - ETL	No
Certification - cULus	Y
Standards - RoHS Compliance Status	CM

## Logistics

Carton Quantity	3000
Minimum Pack Quantity	50

## Product Assets

- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Catalogs - BURNDY Master Catalog - Section G - Wire Management](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Sales Drawings - 30022708](#)
- [Specifications - CT110500SSBL0](#)