



CT110600SSBL, Nylon Cable Tie, 110 lb Tensile Strength, Stainless Steel Barb, 21.18" Long, Natural

By Burndy
Catalog # [CT110600SSBL](#)

Nylon Stainless Steel BARB Cable Ties, 21.18 IN L, .39 IN W,
Tensile Strength: 120 Lbs.



Features

Stainless Steel Barb Tie

Application

For use with self-locking stainless steel barb

General

Catalog Number	CT110600SSBL
Color	Natural
EU RoHS Indicator	Yes
Material	NYLON 6/6
Rating - Minimum Tensile Strength lbs	110
Sub Brand	UNIRAP,CABLE TIE
Trade Name	UNIRAP™
Type	CT_SSB
UPC	781810565445

Dimensions

Dimension - Bundle Diameter Max inch	5.98
Dimension - L Length Overall mm	538 mm
Dimension - Length Overall inch	21.18 in
Dimension - Width inch	0.28 in
Dimension - Width mm	7 mm

Certifications And Compliance

Buy American Compliant	No
Certification - CSA Approved	Yes
Certification - ETL	No
Certification - cULus	Y
Standards - RoHS Compliance Status	CM

Logistics

Carton Quantity	3000
Minimum Pack Quantity	50

Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
[Catalogs - BURNDY Master Catalog - Section G - Wire Management](#)
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
[Sales Drawings - 30022708](#)
[Specifications - CT110600SSBL](#)