



CT110800SSBC, Nylon Cable Tie, 110 lb Tensile Strength, Stainless Steel Barb, 27.52" Long, Natural

By Burndy

Catalog # [CT110800SSBC](#)

Nylon Stainless Steel BARB Cable Ties, 27.52 IN L, .28 IN W, Tensile Strength: 110 Lbs.

Features

Stainless Steel Barb Tie

Application

For use with self-locking stainless steel barb

General

Catalog Number	CT110800SSBC
Color	Natural
EU RoHS Indicator	Yes
Material	NYLON 6/6
Rating - Minimum Tensile Strength N	113
Rating - Minimum Tensile Strength lbs	110 lb
Sub Brand	UNIRAP,CABLE TIE
Trade Name	UNIRAP™
Type	CT-SSB
UPC	781810564905

Dimensions

Dimension - Bundle Diameter Max inch	7.99
Dimension - L Length Overall mm	699 mm



Dimension - Length Overall inch	27.52 in
Dimension - Width inch	0.28 in
Dimension - Width mm	7 mm

Certifications And Compliance

Buy American Compliant	No
Certification - CSA Approved	Yes
Certification - ETL	No
Certification - cULus	Y
Standards - RoHS Compliance Status	CM

Logistics

Carton Quantity	2000
Minimum Pack Quantity	100

Product Assets

- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Catalogs - BURNDY Master Catalog - Section G - Wire Management](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Sales Drawings - 30022708](#)
- [Specifications - CT110800SSBC](#)



A Hubbell brand